

HC00710382 SPD SWITCH 2210-132CC9

By Hubbell Industrial Controls (ICD)
Catalog # [HC00710382](#)



TYPE 2210 SPEED RESPONSIVE SWITCH, C SERIES, CENTRIFUGAL ACTION, FLYWEIGHT OPERATED, NON-DIRECTIONAL AC OR DC CONTACTS, NEMA 9 EXPLOSION-PROOF CLASS 2, GROUPS E, F, OR G

Features

- Rugged Construction
- Snap-Action Contacts or Pneumatic Air Valve
- Oversize Low Friction Bearings
- Surface or Flange Mounting

General

| | |
|----------------|--|
| Catalog Number | HC00710382 |
| Enclosure Type | Fiberglass Reinforced Polyester Resin And/Or Cast Aluminum |
| Series | 2210, C |
| Type | Non-Directional, AC/DC |

Electrical Ratings

| | |
|---------------------------|------|
| Current / Amperage Rating | 10 A |
| Current Rating | 10 A |

Certifications And Compliance

| | |
|-----------------------|---|
| Enclosure NEMA Rating | 9 EXPLOSION-PROOF, CLASS 2, GRP E, F, G, DIV 1, 2 |
|-----------------------|---|

Product Assets

- [Catalogs - 2200/2300 Speed Switches Catalog](#)
- [Catalogs - 2210 Speed Switches Specifications](#)
- [Installation Manuals - ICD_Pub134_CATALOG](#)
- [Installation Manuals - ICD_Pub131_CATALOG](#)
- [Installation Manuals - ICD_Pub130_CATALOG](#)
- [Specifications - HC00710382](#)