



# HC14193100561 TYPE 700 1250 AMP DC CONTACTOR.

By Hubbell Industrial Controls  
Catalog # [HC14193100561](#)

TYPE 700, 1250A DC CONTACTOR WITHOUT OVER CURRENT HOLD-IN (OCHI)



## General

Auxiliary Contacts	1 NO & 3 NC
DC Coil Voltage	74
Maximum break current	2000
Maximum interrupting capacity	1000
Maximum make current	5000
Minimum arc chute clearance	3 in
Mounting Method	Mounts on 2 in. x 3 in. Angle Support with two 3/8 in. screws
Series	700
Through current capability	15000
Type	Definite Purpose

## Dimensions

Weight	10.9 lb
--------	---------

## Electrical Ratings

Amperage Rating	1250 A
Current / Amperage Rating	1250 A
Maximum Current Rating Amps Continuous	1250 Amps @ 40° C ambient
Operating Voltage	1000 VDC
Voltage Rating Description	1000 V

## Product Assets

[Catalogs - 42700 1250 Amp DC Contactor Catalog](#)  
[Catalogs - 100D DC Devices Brochure](#)  
[Installation Manuals - DC Contactor Type 700 Installation, Maintenance, Parts List](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
ICD-HC14193100561-SPEC-EN | REV 1/2024