

**HUBBELL**  
**Industrial Controls**

**HC14193100583 TYPE 700 1250A  
DC CONTACTOR.**

By Hubbell Industrial Controls (ICD)  
Catalog # [HC14193100583](#)

TYPE 700, 1250A DC CONTACTOR WITHOUT OVER CURRENT  
HOLD-IN (OCHI)



**General**

Auxiliary Contacts	3 NO & 1 NC
DC Coil Voltage	125
Maximum break current	2000
Maximum interrupting capacity	1000
Maximum make current	5000
Minimum arc chute clearance	3 in
Mounting Method	Mounts on 2 in. x 3 in. Angle Support with two 3/8 in. screws
Series	700
Through current capability	15000
Type	Definite Purpose

**Dimensions**

Weight	10.9 lb
--------	---------

**Electrical Ratings**

Amperage Rating	1250 A
Current / Amperage Rating	1250 A
Maximum Current Rating Amps Continuous	1250 Amps @ 40° C ambient
Operating Voltage	1000 VDC
Voltage Rating Description	1000 V

**Product Assets**

[Catalogs - 42700 1250 Amp DC Contactor Catalog](#)  
[Catalogs - 100D DC Devices Brochure](#)  
[Installation Manuals - DC Contactor Type 700 Installation,  
Maintenance, Parts List](#)