

**HUBBELL**  
**Industrial Controls**

**HC14193101572 1250A DC CONTACTOR (OCHI).**

By Hubbell Industrial Controls (ICD)  
Catalog # [HC14193101572](#)

TYPE 700, 1250A DC CONTACTOR WITH OVER CURRENT HOLD-IN (OCHI)



**General**

Auxiliary Contacts	2 NO & 2 NC
DC Coil Voltage	96
Maximum break current	2000
Maximum interrupting capacity	1000
Maximum make current	5000
Mounting Method	Mounts on 2 in. x 3 in. Angle Support with two 3/8 in. screws
Operating Temperature Range Celcius	20
Series	700
Type	Definite Purpose

**Dimensions**

Weight	11 lb
--------	-------

**Electrical Ratings**

Amperage Rating	1250 A
Current / Amperage Rating	1250 A
Maximum Current Rating Amps Continuous	1250 Amps @ 40° C ambient
Operating Voltage	1000
Resistance	177
Voltage Rating Description	1000 V

**Product Assets**

- [Catalogs - 42700 1250 Amp DC Contactor Catalog](#)
- [Catalogs - 100D DC Devices Brochure](#)
- [Installation Manuals - DC Contactor Type 700 Installation, Maintenance, Parts List](#)