

**HUBBELL**  
**Industrial Controls**

**HC14193221583 TYPE 716 1600A DC CONTACTOR.**

By Hubbell Industrial Controls (ICD)  
Catalog # [HC14193221583](#)



TYPE 716, 1600A DC CONTACTOR

**General**

Auxiliary Contacts	3 NO & 1 NC
DC Coil Voltage	125
Maximum break current	2400
Maximum interrupting capacity	2400
Maximum make current	10,000
Mounting Method	Mounts on 3 in. wide support with three 3/8 in. screws
Operating Temperature Range Celcius	20
Series	716
Through current capability	30,000
Type	Definite Purpose

**Dimensions**

Weight	27 lb
--------	-------

**Electrical Ratings**

Amperage Rating	1600 A
Current / Amperage Rating	1600 A
Maximum Current Rating Amps Continuous	1600 Amps @ 40°C ambient
Operating Voltage	1500
Resistance	270
Voltage Rating Description	1500 V

**Product Assets**

- [Catalogs - 42716 1600 Amp DC Contactor Catalog](#)
- [Catalogs - 100D DC Devices Brochure](#)
- [Installation Manuals - DC Contactor Type 716 Installation, Maintenance, Parts List](#)