

HC14193757587 TYPE 720 200 AMP
DC CONTACTOR.

By Hubbell Industrial Controls (ICD)
Catalog # [HC14193757587](#)

TYPE 720, 200A DC CONTACTOR

Features

- UL recognized/CSA certified. NEMA Size 4 ½. Polarized arc chutes - standard or high capacity.
- Main Contact Options: SPNO, SPDT, and Series Field Reversal.
- 5 Million mechanical operations. Front access for serviceability.
- Silver alloy main contact tips. AC or DC operation.
- High dielectric and mechanical strength.
- Rugged and reliable, this industrial quality device is used in applications such as gas/oil drilling and solid-state adjustable speed drives, uninterruptible power supplies, fuel cells, crane controls, transit and rail, and mining machinery.
- It is rated at 200 Ampere, continuous at 600 VDC in still air (special voltages available - consult factory) and can achieve a maximum interrupting rating of 600 kW.

General

Arc chute polarity	Negative
Auxiliary Contacts	None
Catalog Number	HC14193757587
DC Coil Voltage	125
Enclosure Type	NEMA 4.5



Mounting Method	Insulated mounting sheet(1/32" thick) provided with contactor
Operating Temperature Range Celcius	20
Series	720
Type	Definite Purpose

Dimensions

Weight	1.68 lb
--------	---------

Electrical Ratings

Amperage Rating	200 A
Current / Amperage Rating	200 A
Operating Voltage	600 VDC
Resistance	226
Voltage Rating Description	600 V

Product Assets

[Catalogs - 100D DC Devices Brochure](#)
[Catalogs - 42720 200 Amp DC Contactor Catalog](#)
[Specifications - HC14193757587](#)