

HC14429464544 TYPE 264 400
AMP CONTACTOR.

By Hubbell Industrial Controls (ICD)
Catalog # [HC14429464544](#)

TYPE 264, 400A DC CONTACTOR

Features

- UL recognized/CSA certified
- Permanent magnet (polarized) arc chutes
- Main Contact Options: SPNO, SPDT, and Series Field Reversal
- 2 Million mechanical operations
- Front access for serviceability
- Silver alloy main contact tips
- AC or DC operation

General

Arc chute polarity	Positive
Auxiliary Contacts	2 NO & 2 NC
Catalog Number	HC14429464544
DC Coil Voltage	125
Mounting Method	Insulated mounting sheet (1/32" thick) provided with
Operating Temperature Range	20
Celcius	
Series	264



TypeDefinite Purpose

Dimensions

Depth	5.687 in
Height	9.03 in
Weight	5.7 lb
Width	4.19 in

Electrical Ratings

Amperage Rating	400 A
Current / Amperage Rating	400 A
Operating Voltage	600
Resistance	507
Voltage Rating Description	600 V

Product Assets

[Catalogs - 100D DC Devices Brochure](#)
[Specifications - HC14429464544](#)