

**HC4245A031200 TYPE 4245 MAN-
MAG DISC SW SIZE 3 AC N12**

By Hubbell Industrial Controls (ICD)
Catalog # [HC4245A031200](#)

TYPE 4245 MANUAL MAGNETIC DISCONNECT SWITCH, NEMA
SIZE 3, 100 AMPS CONTINUOUS, 240/480 VOLTS AC, 3 POLES,
NEMA 12 ENCLOSED, STANDARD FEATURES

Features

- Provides positive manual control for opening contacts
- Provides magnetic control for remote opening of contacts
- Trip-free opening of power contacts
- Contacts are silver faced
- Flange type operating handle has positive “On” and “Off” position

General

Catalog Number	HC4245A031200
Number Of Poles	3
Series	4245 MANUAL-MAGNETIC DISCONNECT
Type	Disconnect Switches

Dimensions

Dimensions	29 in x 15 in x 35 in
------------	-----------------------



Height	35 in
Length	29 in
Width	15 in

Electrical Ratings

Maximum Current Rating Amps	100
Continuous	

Certifications And Compliance

Enclosure NEMA Rating	12
Nema Rating	3

Product Assets

[Catalogs - 4245 Manual-Magnetic Disconnect Switches](#)
[Specifications](#)
[Engineering Drawing - ICD_HC4245A031200401-schematic](#)
[Specifications - HC4245A031200](#)