

**HC4245A051200 TYPE 4245
MANMAG SZ5 AC N12 STANDARD**

By Hubbell Industrial Controls (ICD)
Catalog # [HC4245A051200](#)

TYPE 4245 MANUAL MAGNETIC DISCONNECT SWITCH, NEMA
SIZE 5, 300 AMPS CONTINUOUS, 240/480 VOLTS AC, 3 POLES,
NEMA 12 ENCLOSED, STANDARD FEATURES

Features

- Provides positive manual control for opening contacts
- Provides magnetic control for remote opening of contacts
- Trip-free opening of power contacts
- Contacts are silver faced
- Flange type operating handle has positive “On” and “Off” position

General

| | |
|-----------------|------------------------------------|
| Catalog Number | HC4245A051200 |
| Number Of Poles | 3 |
| Series | 4245 MANUAL-MAGNETIC DISCONNECT |
| Type | Disconnect Switches |

Dimensions

| | |
|------------|-----------------------|
| Dimensions | 33 in x 15 in x 50 in |
|------------|-----------------------|



| | |
|--------|-------|
| Height | 50 in |
| Length | 33 in |
| Width | 15 in |

Electrical Ratings

| | |
|-----------------------------|-----|
| Maximum Current Rating Amps | 300 |
| Continuous | |

Certifications And Compliance

| | |
|-----------------------|----|
| Enclosure NEMA Rating | 12 |
| Nema Rating | 5 |

Product Assets

[Catalogs - 4245 Manual-Magnetic Disconnect Switches](#)
[Specifications](#)
[Engineering Drawing - ICD_HC4245A051200401-SCHEMATIC](#)
[Specifications - HC4245A051200](#)