



HC4245A071200

By Hubbell Industrial Controls
Catalog # [HC4245A071200](#)

TYPE 4245 MANUAL MAGNETIC DISCONNECT SWITCH,
NEMA SIZE 7, 900 AMPS CONTINUOUS, 240/480 VOLTS AC,
3 POLES, NEMA 12 ENCLOSED, STANDARD FEATURES



General

Number Of Poles	3
Series	4245 MANUAL-MAGNETIC DISCONNECT
Type	Disconnect Switches

Dimensions

Dimensions	44 in x 24 in x 70 in
Height	70 in
Length	44 in
Width	24 in

Electrical Ratings

Maximum Current Rating	900
Amps Continuous	

Certifications and Compliance

Enclosure NEMA Rating	12
Nema Rating	7

Product Assets

- [Catalogs - 4245 Manual-Magnetic Disconnect Switches Specifications](#)
- [Catalogs - 4245 Manual-Magnetic Disconnect Switches Price List](#)
- [Engineering Drawing - ICD_HC4245A071200401_B](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
ICD-HC4245A071200-SPEC-EN | REV 1/2024