

**HC4245A081200 TYPE 4245 MAN-  
MAG DISC SW, SZ8 3POLE N12**

By Hubbell Industrial Controls (ICD)  
Catalog # [HC4245A081200](#)

TYPE 4245 MANUAL MAGNETIC DISCONNECT SWITCH, NEMA  
SIZE 8, 1350 AMPS CONTINUOUS, 240/480 VOLTS AC, 3  
POLES, NEMA 12 ENCLOSED, STANDARD FEATURES

**Features**

- Provides positive manual control for opening contacts
- Provides magnetic control for remote opening of contacts
- Trip-free opening of power contacts
- Contacts are silver faced
- Flange type operating handle has positive “On” and “Off” position

**General**

Catalog Number	HC4245A081200
Number Of Poles	3
Series	4245 MANUAL-MAGNETIC DISCONNECT
Type	Disconnect Switches

**Dimensions**

Dimensions	44 in x 24 in x 70 in
------------	-----------------------



Height	70 in
Length	44 in
Width	24 in

**Electrical Ratings**

Maximum Current Rating Amps	1350
Continuous	

**Certifications And Compliance**

Enclosure NEMA Rating	12
Nema Rating	8

**Product Assets**

[Catalogs - 4245 Manual-Magnetic Disconnect Switches](#)  
[Specifications](#)  
[Engineering Drawing - ICD\\_HC4245A081200401-SCHEMATIC](#)  
[Specifications - HC4245A081200](#)