

**HC4245D5A1200 TYPE 4245  
MANMAG DISCONNECT, SZ5A DC  
N12**

By Hubbell Industrial Controls (ICD)  
Catalog # [HC4245D5A1200](#)

TYPE 4245 MANUAL MAGNETIC DISCONNECT SWITCH, NEMA  
SIZE 5A, 400 AMPS CONTINUOUS, 230/250 VOLTS DC, 2  
POLES, NEMA 12 ENCLOSED, STANDARD FEATURES

**Features**

- Prevents accidental application of power.
- Provides positive manual control for opening contacts.
- Provides magnetic control for remote opening of contacts.
- Trip-free opening of power contacts.
- Available in a wide range of ampere ratings.
- Contacts are silver-faced.
- Utilized Euclid standard high quality magnetic contactors.
- Totally front connected.
- Flange type operating handle has positive On and Off position. Provides for Off position padlocking.
- Housed in NEMA Type 12 or 3R enclosures. JIC Door interlock.

**General**

Catalog Number	HC4245D5A1200
Number Of Poles	2
Series	4245 MANUAL-MAGNETIC DISCONNECT
Type	Disconnect Switches



**Dimensions**

Dimensions	33 in x 15 in x 50 in
Height	50 in
Length	33 in
Width	15 in

**Electrical Ratings**

Maximum Current Rating Amps	400
Continuous	

**Certifications And Compliance**

Enclosure NEMA Rating	12
Nema Rating	5A

**Product Assets**

[Catalogs - 4245 Manual-Magnetic Disconnect Switches](#)  
[Specifications](#)  
[Engineering Drawing - ICD\\_HC4245D5A1200401-SCHEMATIC](#)  
[Specifications - HC4245D5A1200](#)