

HC59395010 CONTACTOR SZ5
300A 3 POLE 250V W/ 3 AUXS.

By Hubbell Industrial Controls (ICD)
Catalog # [HC59395010](#)



TYPE 5110 AC CONTACTOR, 300 AMP, 230 VOLT, 3 POLES,
REVERSING, COPPER CONTACTS, WITH MOUNTING PANEL, 3
AUXILIARY CONTACTS

Features

- Convenient DIRECT-WIRING for Right or Left Hand Power Connections, Rugged Terminals on both sides for all power connections
- Completely front-connected, front removable “deadback” base design eliminates all nuts and bolts as well as live parts on the back of the base
- Encapsulated Magnet Coil
- Corrosion resistant, durable, welded steel construction
- armature assembly incorporates stainless steel spring as well as stainless steel hinge pin providing long mechanical life
- Hinged Arc-Shield for easy inspection and replacement of contactor tips Power contact tips

General

Catalog Number HC59395010

Enclosure Type NEMA 5
Series TYPE 5110 AC CONTACTOR

Electrical Ratings

Amperage Rating 300 A
Current / Amperage Rating 300 A
Operating Voltage 250
Voltage Rating Description 230 V

Certifications And Compliance

Nema Rating 5

Product Assets

[Catalogs - 100D DC Devices Brochure](#)
[Specifications - HC59395010](#)