

**HC69ES1Z4060, Pressure Switch**  
**69ES 3 HP 40/60**

By Hubbell Industrial Controls (ICD)  
Catalog # [HC69ES1Z4060](#)



PRESSURE SWITCH 69ES 3 HP 40/60

**Features**

- Contact block replaceable without loss of system pressure
- 100% copper terminals with silver cad-oxide contact points
- Extra wide diaphragm orifice reduces clogging
- Roomy wiring space
- Visible contacts
- Enclosed, state of the art switch mechanism
- Rugged, non-metallic cover
- Two large ground screws
- UL listed & CSA certified
- Optional pulsation orifice

**Application**

Water

**General**

Catalog Number	HC69ES1Z4060
Cut-in pressure	10 psi
Cut-out pressure	80 psi
Differential range	15-25 psi
Horsepower - Maximum	3
Series	69ES

**Product Assets**

[Catalogs - 100P Pressure Switches Brochure](#)  
[Catalogs - 4269ES Pressure Switches](#)  
[Specifications - HC69ES1Z4060](#)