

**HC69ES2BZ1318 PRESSURE
SWITCH ES 5HP 13/18 PSI**

By Hubbell Industrial Controls (ICD)
Catalog # [HC69ES2BZ1318](#)



PRESSURE SWITCH ES 5HP 13/18 PSI

Features

- Contact block replaceable without loss of system pressure
- 100% copper terminals with silver cad-oxide contact points
- Extra wide diaphragm orifice reduces clogging
- Roomy wiring space
- Visible contacts
- Enclosed, state of the art switch mechanism
- Rugged, non-metallic cover
- Two large ground screws
- UL listed & CSA certified
- Optional pulsation orifice

Application

Water

General

Catalog Number	HC69ES2BZ1318
Cut-in pressure	10 psi
Cut-out pressure	80 psi
Differential range	15-25 psi
Horsepower - Maximum	5
Series	69ES

Product Assets

[Catalogs - 100P Pressure Switches Brochure](#)
[Catalogs - 4269ES Pressure Switches](#)
[Specifications - HC69ES2BZ1318](#)