

**HC69WA4Z2040 PRESSURE  
SWITCH ,3HP65 MAX, 20-40 PSI(24**

By Hubbell Industrial Controls (ICD)  
Catalog # [HC69WA4Z2040](#)

PRESSURE SWITCH ,3HP65 MAX, 20-40 PSI(24

**Features**

- Corrosion resistant non-metallic cover
- Straight through wiring
- Visible contacts- 2 pole double break
- No-drift pressure settings
- Easy to adjust
- UL Listed and CSA Certified

**Application**

Water

**General**



Catalog Number	HC69WA4Z2040
Cut-in pressure	5 psi
Cut-out pressure	65 psi
Differential range	15-30 psi
Horsepower - Maximum	3
Series	69W

**Product Assets**

[Catalogs - 100P Pressure Switches Brochure](#)  
[Catalogs - 4269W Pressure Switches Catalog](#)  
[Specifications - HC69WA4Z2040](#)