

**HC69WB5W PRESSURE SWITCH 3  
HP NEMA 3 30-50**

By Hubbell Industrial Controls (ICD)  
Catalog # [HC69WB5W](#)

PRESSURE SWITCH 3 HP NEMA 3 30-50

**Features**

- Corrosion resistant non-metallic cover
- Straight through wiring
- Visible contacts- 2 pole double break
- No-drift pressure settings
- Easy to adjust
- UL Listed and CSA Certified

**Application**

Water

**General**



Catalog Number	HC69WB5W
Cut-in pressure	5 psi
Cut-out pressure	80 psi
Differential range	15-30 psi
Enclosure Type	NEMA 3
Horsepower - Maximum	3
Series	69W

**Product Assets**

[Catalogs - 100P Pressure Switches Brochure](#)  
[Catalogs - 4269W Pressure Switches Catalog](#)  
[Specifications - HC69WB5W](#)