

**HC71241004 POWER LS WITHOUT  
WEIGHT/CABLE**

By Hubbell Industrial Controls (ICD)  
Catalog # [HC71241004](#)

TYPE 4220 POWER LIMIT SWITCH, AC, 2 POLES, N.C.  
CONTACTS, NEMA SIZE 4, RIGHT HAND OPERATION

**Features**

- Positive trigger lock-out
- Direct action contact opening and closing
- One-piece movable contacts
- Exclusive arc transfer action
- Sturdy housing
- Rugged construction

**General**

Catalog Number	HC71241004
Number Of Poles	2
Series	4220 Power Limit Switch
Type	Limit Switch with Copper Contacts



**Electrical Ratings**

Maximum Current Rating Amps 135  
Continuous

**Certifications And Compliance**

Nema Rating 4

**Product Assets**

[Catalogs - 4220 Power Limit Switches Specification](#)  
[Catalogs - 4220 Power Limit Switches Price List](#)  
[Installation Manuals - ICD\\_4220Instr](#)  
[Specifications - HC71241004](#)