

HC91829202 MAGNET CTRLR 100A
SZ3 4296

By Hubbell Industrial Controls (ICD)
Catalog # [HC91829202](#)



TYPE 4296 LIFTING MAGNET CONTROLLER, MANUAL
DISCHARGE RESISTOR, 50-85 AMPS COLD MAGNET CURRENT,
230 VOLTS, 230 VOLTS CONTROL CIRCUIT, NEMA 1A/3R
ENCLOSED

Features

Front-Wired Front-Removable componentsMechanically
interlocked "LIFT" and "DROP" contactorsPermanently
connected discharge path completely independent from the
lineHigh-Thermal capacity resistor discharge pathPeak magnet
induced voltage limited to 600 voltsLong electrical contact
lifeDribble control - StandardVentilated NEMA 3R Enclosure

General

Catalog Number	HC91829202
Series	4296 Euclid
Type	Maunual Discharge

Dimensions

Dimensions	19.12 in x 14.25 in x 30.25 in
------------	--------------------------------

Height	30.25 in
Length	19.12 in
Width	14.25 in

Electrical Ratings

Current / Amperage Rating	50-85 A
---------------------------	---------

Certifications And Compliance

Contactors NEMA Rating	3A
Enclosure NEMA Rating	1A/3R
Nema Rating	NEMA 3R

Product Assets

[Catalogs - 100E Euclid Brochure](#)
[Installation Manuals - ICD_4291Pub180_CATALOG](#)
[Specifications - HC91829202](#)