



# HC91883203

By Hubbell Industrial Controls  
Catalog # [HC91883203](#)

TYPE 4292 YARDMASTER, LIFTING MAGNET CONTROLLER, AUTOMATIC DISCHARGE VARISTOR, 100 AMPS COLD MAGNET CURRENT, 230 VOLTS DC, 24 VOLTS DC CONTROL CIRCUIT, NEMA 1A/3R ENCLOSED



## General

Series 4292 Yardmaster  
Type Automatic Discharge

## Dimensions

Dimensions 19 in x 14 in x 34.25 in  
Height 34.25 in  
Length 19 in  
Width 14 in

## Electrical Ratings

Current / Amperage Rating 100 A

## Certifications and Compliance

Contactor NEMA Rating 3  
Enclosure NEMA Rating 1A/3R

## Product Assets

[Catalogs - 4292P Yardmaster Pup Lifting Magnet Controller Catalog](#)  
[Catalogs - 100E Euclid Brochure](#)  
[Catalogs - 4292 Yardmaster Lifting Magnet Controller Catalog](#)  
[Installation Manuals - ICD\\_4292Pub190\\_CATALOG](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
ICD-HC91883203-SPEC-EN | REV 5/2023