

**HC91883215 4292 MAG CTRLR
PNLSZ3 @115V W/ BATTERY T**

By Hubbell Industrial Controls (ICD)
Catalog # [HC91883215](#)



TYPE 4292 YARDMASTER, LIFTING MAGNET CONTROLLER,
AUTOMATIC DISCHARGE VARISTOR, 100 AMPS COLD MAGNET
CURRENT, 230 VOLTS DC, 115 VOLTS CONTROL CIRCUIT, OPEN
PANEL CONSTRUCTION

Features

- Rated 250 VDC @ 5-100 amps
- Front-Wired Front-Removable components
- Mechanically interlocked “Lift” and “Drop” NEMA rated mill duty contactors
- Permanently connected 700V discharge path completely independent from the line that protects magnet and generator
- High-Thermal capacity varistor discharge path
- Minimum Maintenance
- Ventilated indoor/outdoor NEMA 3R enclosure

General

Catalog Number	HC91883215
Series	4292 Yardmaster
Type	Automatic Discharge

Dimensions

Dimensions	19 in x 14 in x 34.25 in
Height	34.25 in
Length	19 in
Width	14 in

Electrical Ratings

Current / Amperage Rating	100 A
---------------------------	-------

Certifications And Compliance

Contactor NEMA Rating	3
-----------------------	---

Product Assets

[Catalogs - 100E Euclid Brochure](#)
[Catalogs - 4292 Yardmaster Lifting Magnet Controller Catalog](#)
[Catalogs - 4292P Yardmaster Pup Lifting Magnet Controller Catalog](#)
[Installation Manuals - ICD_4292Pub190_CATALOG](#)
[Specifications - HC91883215](#)