



HC91913004 MAGNET CONTROLLER 4296 24V CTL

By Hubbell Industrial Controls
Catalog # [HC91913004](#)



TYPE 4296 LIFTING MAGNET CONTROLLER, MANUAL
DISCHARGE RESISTOR, 13-25 AMPS COLD MAGNET
CURRENT, 230 VOLTS DC, 24 VOLTS CONTROL CIRCUIT,
NEMA 1A/3R ENCLOSED

General

Series 4296 Euclid
Type Manual Discharge

Dimensions

Dimensions 16.12 in x 10 in x 24.25 in
Height 24.25 in
Length 16.12 in
Width 10 in

Electrical Ratings

Current / Amperage Rating 13-25 A

Certifications and Compliance

Contactor NEMA Rating 1
Enclosure NEMA Rating 1A/3R
Nema Rating NEMA 3R

Product Assets

[Catalogs - 4296 Lifting Magnet Controller Specification](#)
[Catalogs - 4296 Lifting Magnet Controller Catalog](#)
[Catalogs - 100E Euclid Brochure](#)
[Installation Manuals - ICD_4291Pub180_CATALOG](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
ICD-HC91913004-SPEC-EN | REV 1/2024