

**HC99875001 LIMIT SW 4225-LS-1950B-WP**

By Hubbell Industrial Controls (ICD)  
Catalog # [HC99875001](#)



TYPE 4225 QUICK BREAK POWER LIMIT SWITCH, AC RATED  
AT 10 HP, DC AT 2.5-5HP, 3 POLES, NEMA 3 WEATHERPROOF

**Features**

- Mill duty construction
- Reversible finger tips and segments for longer life
- Moving and stationary contacts are made from hard drawn copper
- Automatic reset

**General**

Catalog Number                      HC99875001  
Number Of Poles                      3

Series	4225 Quick Break Power Limit Switch
Type	Limit Switch with Copper Contacts

**Certifications And Compliance**

Enclosure NEMA Rating	3
-----------------------	---

**Product Assets**

[Catalogs - 4225 Quick Break Power Limit Switches Specifications](#)  
[Specifications - HC99875001](#)