



HC91883204

By Hubbell Industrial Controls
Catalog # [HC91883204](#)

TYPE 4292 YARDMASTER, LIFTING MAGNET CONTROLLER,
AUTOMATIC DISCHARGE VARISTOR, 100 AMPS COLD
MAGNET CURRENT, 230 VOLTS DC, 24 VOLTS DC CONTROL
CIRCUIT, NEMA 1A/3R ENCLOSED



General

Series	4292 Yardmaster
Type	Automatic Discharge
UPC	782899000810

Dimensions

Dimensions	19 in x 14 in x 34.25 in
Height	34.25 in
Length	19 in
Width	14 in

Electrical Ratings

Current / Amperage Rating	100 A
---------------------------	-------

Certifications and Compliance

Contactors NEMA Rating	3
Enclosure NEMA Rating	1A/3R

Product Assets

[Catalogs - 4292P Yardmaster Pup Lifting Magnet Controller Catalog](#)

[Catalogs - 100E Euclid Brochure](#)

[Catalogs - 4292 Yardmaster Lifting Magnet Controller Catalog](#)
[Installation Manuals - ICD_4292Pub190_CATALOG](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
ICD_HC91883204_SPEC | REV 3/2023