



JIC040403

by Wiegmann
Catalog ID: JIC040403

N12 Handy Box Screw-Cover 4X4X3 Carbon Steel - Gray

Ideal for use where protection from dirt, dust, oil, and water is needed. Particularly suitable for use with liquid-tight flexible conduit.

- Bodies and doors fabricated from 14 gauge steel. Drawn lid which features no welded seams or sharp corners. No holes or conduit knockouts. Cover screws thread into neoprene gasket for maximum sealing. External mounting plates, top and bottom of enclosure. Ground stud located in door. Lids are sealed with closed cell oil resistant neoprene gasket.

Product Details

General

Application	Ideal for use where protection from dirt, dust, oil, and water is needed. Particularly suitable for use with liquid-tight flexible conduit.
Color	Gray
Construction	Seam Welded
Cover Type	Screw Cover
Finish Type	Textured
Listings	UL, CSA
Material	Carbon Steel
Mounting Type	Wall Mount
Type	Enclosure
UPC	786725843473

Dimensions

Depth	3 in
Height	4 in
Weight	2.3 lb
Width	4 in

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none"> • UL • CSA
------------------	---

Nema Rating	NEMA 12
UL Listed	Yes