



# CGB112NB - CGB Series - Unarmored Cable Connector 1/2" NPT Nickel Plated Brass

By Killark  
Catalog # CGB112NB



The CGB connector is for use all unarmored cable and flexible cords. This connector features a removable "top-hat" sleeve seal and is designed to cover a broader range of cable diameters for carrying less stocking SKU's. Superior ingress protection with Type 3,3R,4,4X,12 ratings. Designed and certified for NEC and CEC applications.

## Features

- Revolutionary design covers a broader range of cable sizes
- Grommet sleeves are field removable to adjust to multiple cable ranges and cable diameter variances
- Eliminates carrying numerous amounts of different CGB type connectors for job sites
- Available in sizes ranging from 1/2" to 4" NPT in copper-free aluminum, zinc plated steel, 316L stainless steel and nickel plated brass finishes.

## General

Application	Suitable for use in Class I Divisions 2 when installed in accordance to NEC 501.10(B) (4). Approved for cable use including TC, TC-ER, TC-ER-HL, PLTC, PLTC-ER, ITC, ITC-HL and cords including S, SO, STO, ST, SJ, SJT, SJTO, SVO.
Finish Name	Natural
Ingress Protection	Type 3R, 4, 4X, 12
Material	Nickel Plated Brass
Operating Temperature	- 40C to +80 °C
Series	CGB
UPC	783936180243

## Dimensions

Height	1.7 in
Hub Size	1/2"
Weight	0.15 lb
Width	0.96 in

## Conductor Related

Cable Range	.12 - .354 in
-------------	---------------

## Product Assets

[Catalogs - Killark Catalog](#)



A Hubbell brand