



ENY Series

By Killark
Catalog # [ENY-8](#)

Killark's ENY sealing fittings offers options for installing in both vertical and horizontal positions for harsh hazardous locations. ENY series can make for any sealing needs significant by offering a minimized turn radius for maximized installations. Options are available in copper-free aluminum and Duraloy iron with superior electro-statically applied powder coating for the best corrosive resistance.

Features

- Minimal turn radius for optimal spacing of both enclosures and conduit
- Large openings for ease of access to conductors for proper dam installation
- Engineered to latest 419 hub specifications for superior continuity and ingress protection
- integral bushings to protect conductors during installation

Application

To minimize the passage of gases and vapors from one electrical installation to another through the conduit system. To confine any explosions from sealed enclosures and prevent pressure pilling between conduit systems.

General

Catalog Number	ENY-8
Color	Gray
Finish Type	Powder Epoxy Paint
Material	Copper-free aluminum (less than 4/10 of 1%)
Series	ENY
Type	Sealing Fitting
UPC	783936186610

Dimensions

Height	8.52 in
Hub Size	3"
Weight	4.28 lb
Width	4.125 in

Certifications And Compliance

Hazardous Rating(s)	Class I, Divisions 1 & 2, Groups C, DClass II, Divisions 1 & 2, Groups E, F, GClass III, Divisions 1 & 2
Nema Rating	3R
UL File Number	E10514

Logistics

Carton Quantity	1
-----------------	---

Product Assets

- [3D Models - ENY-8](#)
- [3D Models - KIL_ENY-8](#)
- [Catalog Page - Fittings: EY Series](#)
- [Certifications - ENY Series Sealing Fittings UL Certifications](#)
- [Engineering Drawing - KIL_ENY-8](#)
- [Literature - Hazardous-rated seal-off fittings in expanded trade sizes and with improved design](#)
- [Sales Drawings - KIL_ENY-8](#)
- [Specifications - ENY8](#)

