



SSC Series Solar String Combiner Box

By Killark



SSC Series Solar String Combiner Box

Features

- Lab tested under full load with fuses installed
- Up to 22-String Input from Solar Panels
- Up to 50A Fuse Rating (using up to 80A Finger-Safe Fuse Holder)
- MC4 Quick Connect Connectors (Panel Mount or WhipMount) available to provide faster installation than hard wiring
- Multiple snap latches provide secure latching with lockingfeature
- Gasketed flange O-ring to seal out moisture
- Interlocked rotary handle style operating mechanism withlockout provision as standard
- Adjustable mounting lugs allow for multiple mountingconfigurations (mounting bracket available as optionalselection)
- Surge Protective Device (SPD) offered as optional protection
- Breather Vent / Drain offered as optional weather protection
- Optional safety shield covers all live components
- Bottom Cable Gland location for VE+/VE- output feed topower inverter

General

Cover Type Interlocking

EU RoHS Indicator	Contact Manufacturer
Material	FRP (Fiberglass Reinforced Polyester)
Series	SSC
Temperature Range	-40°C to 50°C

Electrical Ratings

Amperage Rating	<ul style="list-style-type: none">• 400 A• 500 A• 600 A
-----------------	---

Certifications And Compliance

Certification	cETLus 5030724
Industry Standard(s)	<ul style="list-style-type: none">• UL 1741• CSA C22.2 No 290
Nema Rating	3, 4, 4X

Product Assets

[3D Product View - SSC_AR](#)
[Brochures - LBD & SSC Series Brochure](#)
[Catalog Page - SSC Series Catalog Pages](#)
[Installation Manuals - LBD & SSC Series IOM - French](#)
[Installation Manuals - LBD & SSC Series IOM - English](#)



A Hubbell brand