



EXBLTPCA/CB/CD Series Hazardous Location Circuit Breakers

By Killark

EXBLTPCA/CB/CD Series Hazardous Location Circuit Breakers

Features

- Stainless steel metric cover bolts
- O-ring supplied standard for type 4X & IP66 applications
- Standard hinged cover
- Bi-directinal bolt on mounting lugs

General

Color	Gray
EU RoHS Indicator	Contact Manufacturer
Material	Aluminum, Copper Free (less than 4/10 of 1%)

Certifications And Compliance

CSA File Number	LR11716
-----------------	---------



Hazardous Rating(s)

- Class I, Divisions 1 & 2, Groups B, C, D
- Class I, Zones 1 & 2, Groups IIB+H2, IIA
- Class II, Divisions 1 & 2, Groups E, F, G
- Class III Divisions 1 & 2

IP Rating

IP66

Nema Rating

4, 4X

UL File Number

E10514 / E12379 / E83969

Product Assets

[Brochures - EXBLTPCA/CB/CD Series Circuit Breakers Brochure](#)
[Specifications - EXBLTPCA/CB/CD Series Hazardous Location Circuit Breakers](#)



A Hubbell brand