



EXBLTPMS/CMS Series Combination Motor Starters

By Killark



EXBLTPMS/CMS Series Combination Motor Starters

Features

- Stainless steel metric cover bolts
- O-ring supplied standard for type 4X & IP66 applications
- Standard hinged cover
- Bi-directinal bolt on mounting lugs
- Supplied with manual reset buttons and two operator holes with close up plugs
- Three NPT openings in top and bottom

General

Color	Gray
EU RoHS Indicator	Contact Manufacturer
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Series	EXBLTPMS/CMS

Certifications And Compliance

CSA File Number	LR11716
Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Divisions 1 & 2, Groups B, C, D• Class I, Zones 1 & 2, Groups IIB+H2, IIA• Class II, Divisions 1 & 2, Groups E, F, G• Class III Divisions 1 & 2
IECEX File Number	QPS17.0013U / QPS17.0014
IP Rating	IP66
Nema Rating	3, 4, 4X, 7(B, C, D), 9(E, F, G)
UL File Number	E83969

Product Assets

- [Catalog Page - EXBLTPMS/CMS Series Motor Starters Catalog Pages](#)
- [Specifications - EXBLTPMS/CMS Series Combination Motor Starters](#)