



VM4LB6IE230 - VM4LB 6000
Lumen Range Standard with 2000
Lumen Battery Backup 120-277VAC
50/60 Hz

By Killark
Catalog # [VM4LB6IE230](#)



VM4LB 6000 Lumen Range Standard with 2000 Lumen Battery
Backup 120-277VAC 50/60 Hz

General

Catalog Number	VM4LB6IE230
Color Temperature	5000 K
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Light Source	LED
Lumen Range	5,001-10,000 lm
Lumens	6278
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Operating Temperature Range	-20°C to +50°C
Celcius	
Series	VM4L
UPC	783936151731

Electrical Ratings

Lumens Per Watt	157
Voltage Rating	120-277 VAC
Wattage	40 W

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
--------------------------	----------------------

Product Assets

- [Catalogs - Killark Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Specifications - VM4LB6IE230](#)