



VM4LB7IE230 - VM4LB 7000

Lumen Range Standard with 2000

Lumen Battery Backup 120-277VAC

50/60 Hz

By Killark
Catalog # [VM4LB7IE230](#)

VM4LB 7000 Lumen Range Standard with 2000 Lumen Battery
Backup 120-277VAC 50/60 Hz



General

Catalog Number	VM4LB7IE230
Color Temperature	5000 K
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Light Source	LED
Lumen Range	5,001-10,000 lm
Lumens	7437
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Operating Temperature Range	-20°C to +50°C
Celcius	
Series	VM4L
UPC	783936151847

Electrical Ratings

Lumens Per Watt	149
Voltage Rating	120-277 VAC
Wattage	50 W

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
--------------------------	----------------------

Product Assets

- [Catalogs - Killark Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Specifications - VM4LB7IE230](#)



A Hubbell brand