



**VM4LC7IE230 - VM4LC 7000**  
**Lumen Range Standard with 2000**  
**Lumen Battery Backup 120-277VAC**  
**50/60 Hz**

By Killark  
Catalog # [VM4LC7IE230](#)



VM4LC 7000 Lumen Range Standard with 2000 Lumen Battery  
Backup 120-277VAC 50/60 Hz

**General**

Catalog Number	VM4LC7IE230
Color Temperature	5000 K
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Light Source	LED
Lumen Range	5,001-10,000 lm
Lumens	7344
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Operating Temperature Range	-20°C to +50°C
Celcius	
Series	VM4L
UPC	783936151748

**Electrical Ratings**

Lumens Per Watt	147
Voltage Rating	120-277 VAC
Wattage	50 W

**Certifications And Compliance**

Buy America(n) Qualified	Contact Manufacturer
--------------------------	----------------------

**Product Assets**

- [Catalogs - Killark Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Specifications - VM4LC7IE230](#)