



VMLXC LED 15000 LUMEN 120-277V GLASS LEN

By Killark
Catalog # [VMLXC1530G](#)



Application

- Class I Division 2 Hazardous Locations
- Class II Hazardous Dust
- Zone 2 Hazardous Locations
- Off and On Shore Oil and Gas
- Wet and Marine Locations
- Food and Beverage
- Heavy Industrial

General

Catalog Number	VMLXC1530G
Color Temperature	5000 K
Finish Type	Powder Epoxy Paint
Light Source	LED
Lumens	15000
Optic Type	Glass Globe
Series	VMLX-C
UPC	783936186832

Electrical Ratings

Frequency Rating	50-60 Hz
Voltage Rating	120-277 VAC

Wattage	120 W
---------	-------

Certifications And Compliance

Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Div. 2, Groups A, B, C, D• Class I, Zone 2, Groups IIC, IIB, IIA• Class II, Div. 1 & 2, Groups E, F, G• Class III• Suitable for Wet Locations• Type 3, 4X• IP66• Marine Rated (US only)
---------------------	---

Product Assets

- [Brochures - VMLX-C Series](#)
- [Brochures - VMLX-C Series](#)
- [Catalog Page - LIGHTING VMLX-C](#)
- [Installation Manuals - VMLX-VMLXC_IOM](#)
- [Specifications - VMLXC1530G](#)
- [Video - Killark VMLX-C](#)