



WML-X Series LED Area light 40 Watt, 120-277VAC, 5000 Lumen 1-1/4" Straight Stanchion



By Killark
Catalog # [WML1X530S4G](#)

The WML-X area lowbay/highbay light fixture is suitable for harsh and heavy wet location rated environments. The WML-X is designed with improved LED's and pre-installed optics to direct the light where it is needed for various applications. The fixture tank and mounts are made with a cast copper-free aluminum housing and an internal heat sinking driver plate. Easily upgrade outdated HID lighting and help keep facilities operating safely and productively.

Features

- Energy Efficient and Long Life LED's
- Walkway Optic patterns
- Easy Retrofit to Competitors
- Finless Design
- Lighter Weight
- LED Color of 5000K with 80 CRI
- Wildlife Friendly Color options

General

| | |
|--------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number | WML1X530S4G |
| Color Temperature | 5000 K |
| Environmental Conditions | <ul style="list-style-type: none">• Suitablefor Wet Locations• Type 3, 4X• IP66• Marine Rated (US Only) |
| Finish Type | Powder Epoxy Paint |
| Light Source | LED |
| Lumen Range | 5,000 - 9,000 lm |
| Lumens | 5000 |

| | |
|---------------|--------------------|
| Mounting Type | Straight Stanchion |
| Optic Type | Glass Globe |
| Series | WML-X |

Dimensions

| | |
|----------|--------|
| Hub Size | 1-1/4" |
|----------|--------|

Electrical Ratings

| | |
|---------------------------|-------------|
| Current / Amperage Rating | 0.33-0.14 A |
| Frequency Rating | 50-60 Hz |
| Voltage Rating | 120-277 VAC |
| Wattage | 40 W |

Product Assets

- [Brochures - VML-X_Series-WML-X_Series](#)
- [Catalog Page - VMLX&WMLX_Series](#)
- [Photometry - KIL_VML1X530NAR](#)
- [Photometry - KIL_VML1X530N](#)
- [Specifications - WML1X530S4G](#)