



WML-X Series LED Area light 55 Watt, 120-277VAC, 7000 Lumen Driver Tank



By Killark
Catalog # [WML1X730G](#)

The WML-X area lowbay/highbay light fixture is suitable for harsh and heavy wet location rated environments. The WML-X is designed with improved LED's and pre-installed optics to direct the light where it is needed for various applications. The fixture tank and mounts are made with a cast copper-free aluminum housing and an internal heat sinking driver plate. Easily upgrade outdated HID lighting and help keep facilities operating safely and productively.

Features

- Energy Efficient and Long Life LED's
- Walkway Optic patterns
- Easy Retrofit to Competitors
- Lighter Weight
- LED Color of 5000K with 80 CRI
- Wildlife Friendly Color options

General

Catalog Number	WML1X730G
Color Temperature	5000 K
Environmental Conditions	<ul style="list-style-type: none">• Suitablefor Wet Locations• Type 3, 4X• IP66• Marine Rated (US Only)
Finish Type	Powder Epoxy Paint
Light Source	LED
Lumen Range	5,000 - 9,000 lm
Lumens	7000
Optic Type	Glass Globe
Series	WML-X
UPC	783936186924

Electrical Ratings

Current / Amperage Rating	0.46-0.20 A
Frequency Rating	50/60 Hz
Voltage Rating	120-277 VAC
Wattage	55 W

Certifications And Compliance

Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Div2, Groups A,B,C,D• Class I, Zone 2, Groups IIC, IIB, IIA• Class II, Div. 1&2, Groups E,F,G• IECEx QPS 15.0006• Ex ec IIC T4/T3 Gc• Ex tb IIIC T4/T3 Db• QPS22ATEX7000
---------------------	---

Product Assets

[Brochures - VML-X_Series-WML-X_Series](#)
[Catalog Page - VMLX&WMLX_Series](#)
[Specifications - WML1X730G](#)



A Hubbell brand