



WML-X Series LED Area light 75 Watt, 120-277VAC, 9000 Lumen 1" Ceiling Mount

By Killark
Catalog # [WML1X930X3G](#)



The WML-X area lowbay/highbay light fixture is suitable for harsh and heavy wet location rated environments. The WML-X is designed with improved LED's and pre-installed optics to direct the light where it is needed for various applications. The fixture tank and mounts are made with a cast copper-free aluminum housing and an internal heat sinking driver plate. Easily upgrade outdated HID lighting and help keep facilities operating safely and productively.

Features

- Energy Efficient and Long Life LED's
- Walkway Optic patterns
- Easy Retrofit to Competitors
- Finless Design
- Lighter Weight
- LED Color of 5000K with 80 CRI
- Wildlife Friendly Color options

General

Catalog Number	WML1X930X3G
Color Temperature	5000 K
Environmental Conditions	<ul style="list-style-type: none">• Suitablefor Wet Locations• Type 3, 4X• IP66• Marine Rated (US Only)
Finish Type	Powder Epoxy Paint
Light Source	LED
Lumen Range	5,000 - 9,000 lm
Lumens	9000

Mounting Type	Ceiling
Optic Type	Glass Globe
Series	WML-X

Dimensions

Hub Size	1"
----------	----

Electrical Ratings

Current / Amperage Rating	0.63-0.27 A
Frequency Rating	50-60 Hz
Voltage Rating	120-277 VAC
Wattage	75 W

Product Assets

- [Brochures - VML-X_Series-WML-X_Series](#)
- [Catalog Page - VMLX&WMLX_Series](#)
- [Photometry - KIL_VML1X930NDR](#)
- [Photometry - KIL_VML1X930NAR](#)
- [Photometry - KIL_VML1X930N](#)
- [Specifications - WML1X930X3G](#)