



# WML-X Series LED Area light 140 Watt, 120-277VAC, 18000 Lumen 1-1/4" 25° Stanchion Mount

By Killark  
Catalog # [WML2X1830D4G](#)

The WML-X area lowbay/highbay light fixture is suitable for harsh and heavy wet location rated environments. The WML-X is designed with improved LED's and pre-installed optics to direct the light where it is needed for various applications. The fixture tank and mounts are made with a cast copper-free aluminum housing and an internal heat sinking driver plate. Easily upgrade outdated HID lighting and help keep facilities operating safely and productively.

### Features

- Energy Efficient and Long Life LED's
- Walkway Optic patterns
- Easy Retrofit to Competitors
- Finless Design
- Lighter Weight
- LED Color of 5000K with 80 CRI
- Wildlife Friendly Color options

### General

|                          |                                                                                                                                                  |
|--------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number           | WML2X1830D4G                                                                                                                                     |
| Color Temperature        | 5000 K                                                                                                                                           |
| Environmental Conditions | <ul style="list-style-type: none"><li>• Suitablefor Wet Locations</li><li>• Type 3, 4X</li><li>• IP66</li><li>• Marine Rated (US Only)</li></ul> |
| Finish Type              | Powder Epoxy Paint                                                                                                                               |
| Light Source             | LED                                                                                                                                              |
| Lumen Range              | 12,000 - 18,000 lm                                                                                                                               |
| Lumens                   | 18000                                                                                                                                            |



|               |               |
|---------------|---------------|
| Mounting Type | 25° Stanchion |
| Optic Type    | Glass Globe   |
| Series        | WML-X         |

### Dimensions

|          |        |
|----------|--------|
| Hub Size | 1-1/4" |
|----------|--------|

### Electrical Ratings

|                           |             |
|---------------------------|-------------|
| Current / Amperage Rating | 1.17-0.51 A |
| Frequency Rating          | 50-60 Hz    |
| Voltage Rating            | 120-277 VAC |
| Wattage                   | 140 W       |

### Product Assets

[Brochures - VML-X\\_Series-WML-X\\_Series](#)  
[Catalog Page - VMLX&WMLX\\_Series](#)  
[Photometry - KIL\\_VML2X1830NAR](#)  
[Photometry - KIL\\_VML2X1830NDR](#)  
[Photometry - KIL\\_VML2X1830N](#)  
[Specifications - WML2X1830D4G](#)



A Hubbell brand