



# WML-X Series LED Area light 200 Watt, 120-277VAC, 23000 Lumen 3/4" Wall Bracket



By Killark  
Catalog # [WML3X2330B2G](#)

The WML-X area lowbay/highbay light fixture is suitable for harsh and heavy wet location rated environments. The WML-X is designed with improved LED's and pre-installed optics to direct the light where it is needed for various applications. The fixture tank and mounts are made with a cast copper-free aluminum housing and an internal heat sinking driver plate. Easily upgrade outdated HID lighting and help keep facilities operating safely and productively.

### General

Catalog Number	WML3X2330B2G
Color Temperature	5000 K
Environmental Conditions	<ul style="list-style-type: none"><li>• Suitablefor Wet Locations</li><li>• Type 3, 4X</li><li>• IP66</li><li>• Marine Rated (US Only)</li></ul>
Finish Type	Powder Epoxy Paint
Light Source	LED
Lumen Range	23,000 - 28,000 lm
Lumens	23000
Mounting Type	Wall Bracket
Optic Type	Glass Globe
Series	WML-X

### Dimensions

Hub Size	3/4"
----------	------

### Electrical Ratings

Current / Amperage Rating	1.67-0.72 A
Frequency Rating	50-60 Hz
Voltage Rating	120-277 VAC
Wattage	200 W

### Product Assets

[Brochures - VML-X\\_Series-WML-X\\_Series](#)  
[Catalog Page - VMLX&WMLX\\_Series](#)  
[Specifications - WML3X2330B2G](#)