



## WML-X Series LED Area light 250 Watt, 120-277VAC, 28000 Lumen Driver Tank

By Killark

Catalog # [WML3X2830G](#)



The WML-X area lowbay/highbay light fixture is suitable for harsh and heavy wet location rated environments. The WML-X is designed with improved LED's and pre-installed optics to direct the light where it is needed for various applications. The fixture tank and mounts are made with a cast copper-free aluminum housing and an internal heat sinking driver plate. Easily upgrade outdated HID lighting and help keep facilities operating safely and productively.

### Features

- Energy Efficient and Long Life LED's
- Walkway Optic patterns
- Easy Retrofit to Competitors
- Lighter Weight
- LED Color of 5000K with 80 CRI
- Wildlife Friendly Color options

### General

Catalog Number	WML3X2830G
Color Temperature	5000 K
Environmental Conditions	<ul style="list-style-type: none"><li>• Suitablefor Wet Locations</li><li>• Type 3, 4X</li><li>• IP66</li><li>• Marine Rated (US Only)</li></ul>
Finish Type	Powder Epoxy Paint
Light Source	LED
Lumen Range	23,000 - 28,000 lm
Lumens	28000
Optic Type	Glass Globe
Series	WML-X
UPC	783936186986

### Electrical Ratings

Current / Amperage Rating	2.08-0.09 A
Frequency Rating	50/60 Hz
Voltage Rating	120-277 VAC
Wattage	250 W

### Certifications And Compliance

Hazardous Rating(s)	<ul style="list-style-type: none"><li>• Class I, Div2, Groups A,B,C,D</li><li>• Class I, Zone 2, Groups IIC, IIB, IIA</li><li>• Class II, Div. 1&amp;2, Groups E,F,G</li><li>• IECEx QPS 15.0006</li><li>• Ex ec IIC T4/T3 Gc</li><li>• Ex tb IIIC T4/T3 Db</li><li>• QPS22ATEX7000</li></ul>
---------------------	---

### Product Assets

[Brochures - VML-X\\_Series-WML-X\\_Series](#)  
[Catalog Page - VMLX&WMLX\\_Series](#)  
[Specifications - WML3X2830G](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved  
KILL-WML3X2830G-SPEC-EN | REV 3/2025