

By Killark

Catalog # [2FDC-2M](#)

3/4" Iron, 2FDC Type Two Gang Deep Device Box



## Features

- Tapered threads (NPT with integral bushings)
- Internal grounding screw
- Mounting feet are provided as standard
- Suitable for use in wet locations when used with gasket covers
- Cast iron is suitable for concrete use

## Application

Accommodates wiring devices and provides opening to splice, tap, or pull conductors. Provide access to conductors for maintenance and future system changes.

## Specifications

EU RoHS Indicator	Contact Manufacturer
Nema Rating	3, 4
UL File Number	E3397
CSA File Number	LR11852

## Configuration

Number Of Outlets	2
-------------------	---

## Hub Pattern

## Feed-Thru

## Dimensions

Gross Weight with Packaging	3.84
Hub Size	3/4"
Width	6 in
Height	4 in
Length	7.625 in
Dimensions	7.625 in x 6 in x 4 in

## General

Type	Device Box
Material	Iron
UPC	783936048666
Color	Gray

## Operational

Temperature Rating	-50°C to +60°C
--------------------	----------------

## Product Assets

[Catalog \[English\]](#)