



2GCBB-20Q13 - GCBB Series, AL Feed-Thru Circuit Breaker Load Ctr, 20A Trip Quicklag, One 1-Pole and One 3-Pole, 120/240VAC, Hub Size 3/4"-14 NPT

By Killark
Catalog # 2GCBB-20Q13



GCBB Series - Aluminum Feed-Thru Circuit Breaker Load Center with Cutler-Hammer Circuit Breaker- 20A Trip Quicklag- One 1-Pole and One 3-Pole- 120/240VAC- Hub Size 3/4"-14 NPT.

General

| | |
|-----------------------------------|--|
| Application | |
| Catalog Number | 2GCBB-20Q13 |
| EU RoHS Indicator | Contact Manufacturer |
| Enclosure Type | Threaded |
| Material | Aluminum, Copper Free (less than 4/10 of 1%) |
| Mounting Type | |
| Number Of Poles | 4 |
| Operating Temperature Celcius Max | 40 Degree |
| Series | GCBB |
| Type | |
| UPC | 783936205199 |

Dimensions

| | |
|-----------------------------|-------------------------------|
| Depth | 6.625 |
| Diameter - Inside | 0.88 in |
| Dimensions | 11.5 in x 8.125 in x 6.875 in |
| Gross Weight with Packaging | 12.4 |
| Height | 6.875 in |
| Length | 11.5 in |
| Weight | 12 lb |
| Width | 8.125 in |

Electrical Ratings

| | |
|------------------|-------|
| Frequency Rating | 60 Hz |
|------------------|-------|

Certifications And Compliance

| | |
|---------------------|---|
| Hazardous Rating(s) | Class I, Divisions 1 & 2, Groups B, C, D Class I, Zones 1 & 2, Groups IIB+H2, IIA Class II, Divisions 1 & 2, Groups E, F, G Class III, Divisions 1 & 2 |
| Nema Rating | 3R, 7(B, C, D), 9(E, F, G) |
| UL File Number | E83969 |

Product Assets

[Customer Notices - Prop 65 Notice](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
KILL_CA-2GCBB20Q13-SPEC-EN | REV 6/2024