



AN-10 - 4" Aluminum, Rigid Conduit Nipple

By Killark
Catalog # [AN-10](#)

4" Aluminum, Rigid Conduit Nipple.



*Representative Image

Features

- Tapered threads (NPT) meet latest UL 1203 requirements

Application

To connect threaded or IMC conduit to cast hubs on drilled and tapped conduit openings

General

Color	<ul style="list-style-type: none">• Silver• Argent
Finish Type	Naturel
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Series	AN
Type	<ul style="list-style-type: none">• Rigid Conduit Nipple• Rigid Conduit Nipple
UPC	783936012889

Dimensions

Dimensions	3.46 in x 4.334 in x 4.334 in
Gross Weight with Packaging	0.9
Height	4.334 in
Hub Size	4"
Length	3.46 in
Width	4.334 in

Certifications and Compliance

Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Divisions 1 & 2, Groups A, B, C, D• Class II, Divisions 1 & 2, Groups E, F, G• Class III, Divisions 1 & 2
UL File Number	E311892

Product Assets

- [3D Models - AN-10 3D Model \(STP\)](#)
- [Catalogs - Killark Catalog](#)
- [Certifications - AN Series UL Certificate of Compliance](#)
- [Customer Notices - Prop 65 Notice](#)
- [Engineering Drawing - AN-10 Engineering Drawing \(DWG\)](#)
- [Installation Manuals - AN Series Nipples IOM K141I](#)
- [Sales Drawings - AN-10 Sales Drawing \(PDF\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
KILL_CA-AN-10-SPEC-EN | REV 1/2024