



B7010SK

By Killark
Catalog # [B7010SK](#)

Size 0, Square D, 3 Pole 3 Wire Magnetic Motor Starter 480V
Coil.



*Representative Image

Features

- Type 4, 4X rated – providing protection from hose directed water and corrosion.
- Universal mounting pan, pre-drilled to facilitate easy field installation of starters.
- Provision for grounding supplied as standard.
- More wiring room meets latest NEC wire bend requirements.
- Quick release, captivated, 316 grade stainless steel cover bolts.
- Flange sealing gasket located to the inside of cover bolt to prevent water seepage into enclosure through bolt holes.
- Hinged cover provided as standard for an extra measure of safety and convenience.
- Breaker (MCP) handle can be padlocked in “ON” or “OFF” position.
- Provisions provided for drain and breather plus conduit openings for power and control.
- Reset button provided as standard.
- Two control operator openings provided plugged as standard.
- Additional openings can be factory or field drilled.
- Copper-free (less than 4/10 of 1% copper) enclosure.
- Bolt on bi-directional ductile mounting lugs.

General

EU RoHS Indicator	Contact Manufacturer
Horsepower - Maximum	5
Series	B7
UPC	783936095523

Electrical Ratings

Coil Voltage	480V
Voltage Rating	600 V

Certifications and Compliance

CSA File Number	LR11714
Hazardous Rating(s)	<ul style="list-style-type: none">• Class I, Divisions 1 & 2, Groups B, C, D• Class I, Zones 1 & 2, Groups IIB+H2, IIA• Class II, Divisions 1 & 2, Groups E, F, G• Class III, Divisions 1 & 2
Nema Rating	3, 4, 4X
UL File Number	E83696

Product Assets

[Certifications - B7 Series Enclosure UL Certifications](#)
[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - KIL_B7011 Series Mounting Pan IOM_K1056](#)



A proud member of the Hubbell Family.