



B7010SM - Size 0, Square D, 3 Pole 3 Wire Magnetic Motor Starter 600V Coil

By Killark
Catalog # B7010SM

Size 0, Square D, 3 Pole 3 Wire Magnetic Motor Starter 600V
Coil.



*Representative Image

Features

- Reset button provided as standard.
- Two control operator openings provided plugged as standard.
- Additional openings can be factory or field drilled.
- Copper-free (less than 4/10 of 1% copper) enclosure.
- Bolt on bi-directional ductile mounting lugs.

General

Catalog Number	B7010SM
EU RoHS Indicator	Contact Manufacturer
Horsepower - Maximum	5
Series	B7
Size	0
UPC	783936095530

Electrical Ratings

Coil Voltage	600V
Voltage Rating	600 V

Certifications And Compliance

CSA File Number	LR11714
Hazardous Rating(s)	Class I, Divisions 1 & 2, Groups B, C, D Class I, Zones 1 & 2, Groups IIB+H2, IIA Class II, Divisions 1 & 2, Groups E, F, G Class III, Divisions 1 & 2
Nema Rating	3, 4, 4X
UL File Number	E83696

Product Assets

[Certifications - B7 Series Enclosure UL Certifications](#)
[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - KIL_B7011 Series Mounting Pan IOM_K1056](#)



A Hubbell brand