



B7011 - B7 Series- Motor Starter- NEMA Size 0/1

By Killark
Catalog # B7011

B7 Series- Motor Starter- NEMA Size 0/1.



*Representative Image

Features

- Reset button provided as standard.
- Two control operator openings provided plugged as standard.
- Additional openings can be factory or field drilled.
- Copper-free (less than 4/10 of 1% copper) enclosure.
- Bolt on bi-directional ductile mounting lugs.

General

Application	
Catalog Number	B7011
EU RoHS Indicator	Contact Manufacturer
Material	Copper-free aluminum
Series	B7
Size	1
Type	
UPC	783936020006

Dimensions

Dimensions	4.5 in x 1 in x 6.5 in
Gross Weight with Packaging	46
Height	6.5 in
Length	4.5 in
Width	1 in

Electrical Ratings

Voltage Rating	600 V
----------------	-------

Certifications And Compliance

CSA File Number	LR11714
Hazardous Rating(s)	Class I, Divisions 1 & 2, Groups B, C, D Class I, Zones 1 & 2, Groups IIB+H2, IIA Class II, Divisions 1 & 2, Groups E, F, G Class III, Divisions 1 & 2
Nema Rating	3, 4, 4X
UL File Number	E83696

Product Assets

- [Catalogs - Killark Catalog](#)
- [Certifications - B7 Series Enclosure UL Certifications](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - KIL_B7011 Series Mounting Pan IOM_K1056](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
KILL_CA-B7011-SPEC-EN | REV 6/2024