



## B7011HG - Size 1, Cutler-Hammer, 3 Pole 3 Wire Magnetic Motor Starter 230V Coil

By Killark  
Catalog # B7011HG

Size 1, Cutler-Hammer, 3 Pole 3 Wire Magnetic Motor Starter  
230V Coil.



\*Representative Image

### Features

- Reset button provided as standard.
- Two control operator openings provided plugged as standard.
- Additional openings can be factory or field drilled.
- Copper-free (less than 4/10 of 1% copper) enclosure.
- Bolt on bi-directional ductile mounting lugs.

### General

Catalog Number	B7011HG
EU RoHS Indicator	Contact Manufacturer
Horsepower - Maximum	7.5
Series	B7
Size	1
UPC	783936095554

### Electrical Ratings

Coil Voltage	240V
Voltage Rating	600 V

### Certifications And Compliance

CSA File Number	LR11714
Hazardous Rating(s)	Class I, Divisions 1 & 2, Groups B, C, D  Class I, Zones 1 & 2, Groups IIB+H2, IIA  Class II, Divisions 1 & 2, Groups E, F, G  Class III, Divisions 1 & 2
Nema Rating	3, 4, 4X
UL File Number	E83696

### Product Assets

- [Catalogs - Killark Catalog](#)
- [Certifications - B7 Series Enclosure UL Certifications](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - KIL\\_B7011 Series Mounting Pan IOM\\_K1056](#)



A Hubbell brand