



B7NFD16A - B7NFD Series - Aluminum Feed-Thru Compact Non-Fused Disconnect Switch Enclosure with ABB Switch - 16A/3P/600VAC/50HP Max

By Killark
Catalog # B7NFD16A



*Representative Image

B7NFD Series - Aluminum Feed-Thru Compact Non-Fused Disconnect Switch Enclosure with ABB Switch - 16A/3P/600VAC/50HP Max.

Features

- ABB UL508 certified switch supplied for 600VAC, 16, 32, 40, 63 & 80 Amp unit available.
- Enclosures - Copper-free cast aluminum (less than 4/10 of 1% copper content).
- Cover bolts 316 Stainless Steel
- Silicone O-ring gasket.
- Gray powder polyester painted exterior, electrostatically applied.

General

Action	3P
Actuator	Rotary Handle
Catalog Number	B7NFD16A
Color	
EU RoHS Indicator	Contact Manufacturer
Enclosure Type	Bolted
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Mounting Type	
Number Of Poles	3
Operating Temperature Celcius Max	40 Degree
Series	B7NFD
Type	
UPC	783936151687

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	600 VAC

Conductor Related

Number Of Wires	4
-----------------	---

Certifications And Compliance

CSA File Number	LR11714
Hazardous Rating(s)	Class I, Divisions 1 & 2, Groups B, C, D Class I, Zones 1 & 2, Groups IIB+H2, IIA Class II, Divisions 1 & 2, Groups E, F, G Class III, Divisions 1 & 2
Nema Rating	3, 4, 4X, 7(B, C, D), 9(E, F, G)

Product Assets

- [3D Models - B7NFD1 3D Model](#)
- [Catalogs - Killark Catalog](#)
- [Certifications - B7MS, B7MSN, & B7NFD Series CSA Certification](#)
- [Customer Notices - Prop 65 Notice](#)
- [Engineering Drawing - B7NFD1 Engineering Drawing](#)
- [Installation Manuals - B7NFD1-2 IOM K1328](#)
- [Installation Manuals - B7NFD Series IOM K1327](#)
- [Sales Drawings - B7NFD1 Sales Drawing](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
KILL_CA-B7NFD16A-SPEC-EN | REV 6/2024