



CGB0334SA - CGB Series - Unarmored Cable Connector 4" NPT Aluminum

By Killark
Catalog # [CGB0334SA](#)

The CGB connector is for use all unarmored cable and flexible cords. This connector features a removable "top-hat" sleeve seal and is designed to cover a broader range of cable diameters for carrying less stocking SKU's. Superior ingress protection with Type 3,3R,4,4X,12 ratings. Designed and certified for NEC and CEC applications.



Features

- Revolutionary design covers a broader range of cable sizes
- Grommet sleeves are field removable to adjust to multiple cable ranges and cable diameter variances
- Eliminates carrying numerous amounts of different CGB type connectors for job sites
- Available in sizes ranging from ½" to 4" NPT in copper-free aluminum, zinc plated steel, 316L stainless steel and nickel plated brass finishes.

General

Finish Name	Natural
Ingress Protection	Type 3R, 4, 4X, 12
Material	Aluminum
Operating Temperature	- 40C to +80 °C
Series	CGB
UPC	783936184807

Dimensions

Hub Size 4"

Conductor Related

Cable Range 3.34 - 3.74 in

Product Assets

[Certifications - KIL_CGB UL Certificate_UL](#)



A proud member of the Hubbell Family.