



# CGB115 - CGB Series - Unarmored Cable Connector 1/2" NPT Zinc Plated Steel

By Killark  
Catalog # [CGB115](#)



The CGB connector is for use all unarmored cable and flexible cords. This connector features a removable "top-hat" sleeve seal and is designed to cover a broader range of cable diameters for carrying less stocking SKU's. Superior ingress protection with Type 3,3R,4,4X,12 ratings. Designed and certified for NEC and CEC applications.

## Features

- Revolutionary design covers a broader range of cable sizes
- Grommet sleeves are field removable to adjust to multiple cable ranges and cable diameter variances
- Eliminates carrying numerous amounts of different CGB type connectors for job sites
- Available in sizes ranging from 1/2" to 4" NPT in copper-free aluminum, zinc plated steel, 316L stainless steel and nickel plated brass finishes.

## General

Catalog Number	CGB115
Finish Name	Natural
Ingress Protection	Type 3R, 4, 4X, 12
Material	Steel
Operating Temperature	- 40C to +80 °C
Series	CGB
UPC	783936184524

## Dimensions

Hub Size 1/2"

## Conductor Related

Cable Range .157 - .472 in

## Product Assets

- [3D Models - CGB115 3D Model](#)
- [3D Models - CGB115 3D Model](#)
- [Brochures - Killark CGB Gland Flyer - English](#)
- [Brochures - CGB Series A Revolutionary Cable Connector for Industrial and Hazardous Applications](#)
- [Brochures - Killark CGB Gland Flyer - French](#)
- [Catalog Page - CGB Glands Catalog](#)
- [Catalogs - Killark Catalog](#)
- [Certifications - KIL\\_CGB UL Certificate\\_UL](#)
- [Engineering Drawing - CGB115 Engineering Drawing](#)
- [Sales Drawings - CGB115 Sales Drawing](#)
- [Specifications - CGB115 Specification Sheet English](#)
- [Specifications - CGB115 Specification Sheet French](#)
- [Video - CGB Series Introduction](#)



A Hubbell brand